



FOR GOOD REASONS

panDOMO[®] SP-F

Porefiller

Water based acrylic and urethane containing primer

Priming of polished and oiled floors prior to the application of PANDOMO[®] SP-GS sealer.

Interior

Fast drying

Easy to apply

High yield



Reg. No. 37344

Manufacturer
with certified quality system
as per DIN EN ISO 9001

ARDEX GmbH
58430 Witten · P.O. Box 6120
GERMANY
Telephone: +49 (0) 23 02/664-0
Telefax: +49 (0) 23 02/664-437
kundendienst@ardex.de
www.ardex.de

panDOMO® SP-F

Porefiller

Use:

Priming of polished and oiled floors prior to the application of PANDOMO® SP-GS sealer. PANDOMO® SP-F Porefiller penetrates into the pores of the substrate and forms a film. This provides a homogenous absorption of the substrate, and helps to apply the PANDOMO® SP-GS Sealer. The surface remains water vapour permeable. Can not be used as penetrating sealer (Topcoat).

Description:

Liquid-cloudy, whitish water based acrylic and urethane containing primer.

Application:

In case PANDOMO® SP-SL Stone oil has been applied before, the layer has to dry for at least 12 hours. (See technical data sheet). Apply on the dry surface PANDOMO® SP-F undiluted, homogenously and thin. Do not wipe into the PANDOMO® SP-F. Avoid puddles. In most cases a single coat will be enough. If a further coat has to be installed wait at least for 4 hours.

Important:

PANDOMO® SP-SL which has not dry completely will lead to white discoloration of the PANDOMO® SP-F Pore filler. The discoloration will disappear after drying.

Health and safety/disposal:

Keep out of reach from children

Container and content/dispose according to local/regional/national and international laws.

Technical data according to ARDEX quality standards:

Material requirement:	approx. 25-50 ml/m ²
Density:	approx. 1,0 g/cm ³
PH-Value:	approx. 8
Flash point:	n.a.
Water solveable:	completely
Application temperature:	approx. + 15 - + 25°C Surfacetemperature. Underfloorheating the temperature has be lowered of switched off.
Drying time:	Touch dry after 30 minutes. Trafficable after 2 hours Lower temperatures will prolong the drying.
Cleaning of the tools:	Immediately after use with water
Marking acc. GHS/CLP:	None
Marking acc. GGVSEB/ADR:	None
GISCODE:	GE 10
Packaging:	Plastic container 5 L net
Storage :	cool, but free from frost. Close tightly after usage.
Shelf life:	can be stored for approximately 12 months in dry rooms in unopened packaging.

We assume the warranty for the perfect quality of our products. Our handling recommendations are based on trials and practical experience; they can, however, only be regarded as general advice without a quality warranty, as we have not influence on work site conditions and the execution of the work.
Country specific recommendations, depending on local standards, codes of practice, building regulations or industry guidelines, may affect specific installation recommendations